


PQC:

Bidder or OEM should have experience of supply of glass level gauge. Bidder has to submit at least one PO copy of the same supplied by them or by their OEM, in last five year from the tender due date.


8.1.2020
उमेश के. गुप्ता / Umesh K. Gupta
उप प्रबंधक / Dy. Manager
जी.पी.एक्स. / G.P.X.
बी.एच.ई.एल., भोपाल / BHEL, BHOPAL

Specification

Item No.	Item description	Quantity	Vendor to confirm/Specify
1	Tubular type level gauge glass & spare valve set as per below: (A) Tubular type level gauge glass consisting of glass tube, tube protector, top isolating valve with vent plug & bottom isolating valves with drain, Application: hydrochloric acid (concentration 40 %) , as per following details. Centre to centre distance: 2100 mm, process connection: 1" flanged as per BS table 10 D, Drain and isolating valve material: Polypropylene, Valve body and internals material: Polypropylene, Stud's material: Polypropylene, Glass: 19 mm OD transparent borosilicate glass, Scale: Stainless steel/non-metallic, glass tube protector: non-metallic brackets. (B) Spare isolating valves set: One set consisting of 1no. Top side isolating valve + 1 no. bottom side valve.	02 set { 2 set of gauge glass as per (A) + 2 set of spare isolating valves as per (B) }	
2	Tubular type level gauge glass & spare valve set as per below: (A) Tubular type level gauge glass consisting of glass tube, tube protector top isolating valve with vent plug & bottom isolating valves with drain, Application: caustic lye, as per following details. Centre to centre distance: 1500 mm, process connection: 1" flanged as per BS table 10 D, Drain and isolating valve material: Polypropylene, Valve body and internals material: Polypropylene, Stud's material: Polypropylene, Glass: 19 mm OD transparent borosilicate glass, Scale: Stainless steel/non-metallic, glass tube protector: non-metallic brackets. (B) Spare isolating valves set: One set consisting of 1no. Top side isolating valve + 1 no. bottom side valve.	02 set { 2 set of gauge glass as per (A) + 2 set of spare isolating valves as per (B) }	
3	Tubular type level gauge glass & spare valve set as per below: (A) Tubular type level gauge glass consisting of glass tube, tube protector top isolating valve with vent plug & bottom isolating valves with drain, Application: hydrochloric acid (concentration 40 %) , as per following details. Centre to centre distance: 700 mm, process connection: 1" flanged as per BS table 10 D, Drain and isolating valve material: Polypropylene, Valve body and internals material: Polypropylene, Stud's material: Polypropylene, Glass: 19 mm OD transparent borosilicate glass, Scale: Stainless steel/non-metallic, glass tube protector: non-metallic brackets. (B) Spare isolating valves set: One set consisting of 1no. Top side isolating valve + 1 no. bottom side valve.	04 set { 4 set of gauge glass as per (A) + 4 set of spare isolating valves as per (B) }	

 **Umesh K. Gupta**
 Dy. Manager / G.P.X.
 BHEL, BHOPAL